



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Docking station for up to 4 pumps B.BRAUN 8713140 (Reconditioned)

Used, very good technical condition,

Germany production,

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 80 VA,

It has a comfortable handle to move,

It has a mounting place for the bracket, with which it is possible to mount it on a tripod (no bracket included),

Dimensions: 280 x 210 x 360 mm,

Cat.02

He has a current Technical Passport issued,

Warranty:

6 months for the domestic market - Poland,

1 month for the international market,

Possibility of financing (Poland only): Installments, Leasing, Loan.

