



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



VDW BEEFILL 2in1 Gutta-Percha for thermoplastic obturation kit (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Germany (2011),
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- **VDW BeeFill 2in1** is a kit designed for thermoplastic root canal filling with gutta-percha. BeeFill guarantees extremely durable and tight fillings - three-dimensional, dense and durable - of root canals, which can be performed in a very fast and extremely hygienic way,
- **Advantages:**
 - Large and easy-to-read control panel screen divided into filling the apical section (Downpack) and the middle and coronal parts (Backfill),
 - Simple button navigation,
 - Possibility to modify settings according to individual needs,
 - Programming buttons to save preferred settings,
 - Ergonomic handle for 360° operation around the axis,
 - Simple activation with flexible sensor ring,
 - Perfectly visible root canal outlet thanks to the device's slender handle and extra-long cannula,
 - Precise gutta-percha dosage controlled by the micro-motor,
 - Acoustic and visual monitoring of device performance,
- **Effective root canal filling of any tooth:**
 - High efficiency (90%) of root canal filling with instant vertical condensation technique,
 - Permanent sealing of the entire root canal system,
 - Uniform and dense filling,
 - Minimal risk of root fracture,
 - Possibility of restoration with adhesive materials in one visit,
- **In the set:**
 - Pack handle,
 - Fill handle,
 - Machtou hand pluggers - 3 pcs:
 - 1 - 2 size,
 - 3 - 4 size,
 - 0 (NiTi) size,
 - Thermal tip,
 - Multilingual instruction manual (PDF),
 - Power cord,
- Overall dimensions: 16 x 16 x 15,5 (22 with a handle) cm,
- Set's weight: 2 kg,
- Cat 02,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport (service report),**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

