



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NIKON NL-30 automatic lensmeter (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 50 VA,
- **NIKON NL-30 lensmeter** is characterized by very easy operation, high quality construction as well as fast and accurate measurement,
- **Specification:**
 - Sphere (S): $S \pm 30D$ (step in 0.12D or 0.25D increments),
 - Cylinder (C): $C \pm 12D$ (S+C; less than 40D), (step in 0.12 or 0.25D increments),
 - Axis: 0-180° (1° step),
 - Prism (P):
 - 3 directional: up/down input/output (Px-Py), R0, mm distance,
 - Horizontal 1-10 Δ (step in 0.12 or 0.25 Δ increments),
 - Vertical: 1-10 Δ ,
 - Vector: 1-10 Δ ,
 - Base: 1-360° (1° step),
 - Decentering: 160mm (vertical), 160mm (horizontal),
 - Magnification: 0 to 10D (step in 0.12 or 0.25 increments),
 - R/L indication: Automatic by touch sensor,
 - Optical beam diameter: 3mm,
 - Light source: red LEDs (x4) (660nm),
 - Transmission ratio: 10% or more (at 660nm beam),
 - Measurement time: within 2 seconds,
 - Interface: RS-232C,
 - Display: LCD with backlight,
 - Contact lens: hard glass mode/soft glass mode,
 - Progressive lens: Continuous reading,
 - Lens diameter: 4 - 100 mm,
 - Printer: thermal printing,
 - Paper width: 60 mm,
- It has normal signs of use,
- **English menu,**
- **English keyboard on the control panel,**
- **In the set:**
 - English instruction manual (PDF),
 - Power cord,
- Dimensions: 25 x 27 x 46 cm,
- Weight: 10 kg,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport (service report),**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

