



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **TOPCON KR-8800 Auto kerato - refractometer (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Japan,
- Power supply: 240 V,
- Frequency: 50/60 Hz,
- Power: 75 VA,
- Auto kerato - refractometer provides highly accurate measurement of spherical refraction, power and cylinder axis. It has a keratometry function - measuring the curvature of the anterior corneal surface,
- 5" color LCD monitor,
- Automatic measurement mode,
- Refraction measurement parameters:
  - Sphere range: from -25D to +22D measurement with 0.25D or 0.12D step,
  - Cylinder range: 0 to  $\pm 10$ D measurement with 0.25D or 0.12D step,
  - Axis step: 0° - 180° measurement with a step of 1° or 5°,
  - Minimum pupil diameter: 2.00mm,
- Corneal curvature measurement parameters:
- Radius measurement range: 5.00mm to 10mm measurement with 0.01mm step,
- Refractive index: 1.3375,
- Corneal refraction measurement range: from 67.5D to 33.75D measurement with a step of 0.25D or 0.12D,
- Corneal astigmatism: 0 to  $\pm 10$ D measurement with 0.25D or 0.12D step,
- Axis step: 0° to 180° measurement with a step of 1° or 5°,
- Measurement diameter: 3mm for 7.7mm curvature,
- Features built-in thermal printer with paper diameter: 5.5 cm,
- Manual chin adjustment within 7 cm,
- Built-in USB output port,
- Includes:
  - User manual in English (PDF),
  - Power cord,
- Dimensions: 27.5 x 47.5 x 45.0 cm,
- Weight: 20 kg,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN DUTCH

Мы говорим по русски

Мы говорим по украински

