



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



TOMEY TL-3000C Electronic dioptrimeter (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Japan, (2011),
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 55 VA,
- The TL-3000C dioptrimeter can measure standard and high times, bifocal and trifocal as well as progressive and prism. In addition, we can measure hard and soft contact lenses,
- A color touch panel and customizable shortcut buttons allow us to work on the device with ease,
- The 3000c has simultaneous measurement of UV transmittance (385 nm) while measuring lens power.
- Using PD mode, the TL-3000C has the ability to measure the distance between the pupils of the eye using automatic right/left detection,
- AUTO CL mode,
- Menu in language: EN,
- Technical specifications:
 - Display:
 - Diagonal: 5.7 ",
 - Resolution: 320 x 240 px,
 - Built-in printer:
 - Print diameter: 38 mm,
 - Measurement range:
 - Sphere: - 25 to +25D,
 - Cylinder: - 9.99 to + 9.99D,
 - Axis: 0° to 180°,
 - Adjacency: from 0 to 9.99D,
 - Prism: from 0 to 10D,
 - Measurement step:
 - Diopter: 0.01/0.12/ 0.25D,
 - Prism: 0.01/0.12/ 0.25D,
 - Measurement modes:
 - Cylinder: +/- , Mixed,
 - Prism: rectangular coordinates, polar wsp,
 - Measured glasses:
 - Ocular lens,
 - Contact lens,
 - Optical lens,
 - Measured glass diameters:
 - 20 to 100 mm,
 - ABBE numbers:
 - 30, 35, 40, 45, 50, 55, 60, 65,
 - Has inputs:
 - USB,
 - D-SUB - 9pin,
- Includes:
 - User manual in English (PDF),
 - Power cord,
- Dimensions: 22 x 26 x 44 cm,
- Weight: 7 kg,
- Has a current inspection and is ready for use,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

