



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **CARL ZEISS PLUS Colposcope (4K vision track) (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 140 VA,
- CARL ZEISS PLUS is a mobile colposcope equipped with 4K quality vision track,
- Specifications:
  - Light source: halogen bulb: 12 V / 100 W,
  - Fiber optic,
  - Magnification: 0.6x, 1x, 1.6x,
  - Eyepiece spacing adjustment in range: 55 to 80 mm,
  - Eyepiece: 12.5x,
  - Focal length (f): 250,
  - Infinitely adjustable:
    - Light intensity,
    - Eyepiece height in range: 60 to 125 cm,
- Free adjustment of the colposcope in a wide range by means of a fixed handle,
- There are knobs on the pantographic arm to lock the colposcope in the selected position,
  - Colposcope expanded with 4K video track, which includes:
    - SONY CMOS 4K Camera:
      - Sensor: Sony 1/2.8 inch, CMOS sensor with 8.29 million pixels,
      - Pixel size: 1.45 µm x 1.45 µm,
      - HDMI Output: 3840x2160 at 30 frames/1920x1080 at 60 frames,
      - USB output: 3840x2160 / 2560x1440 / 1920x1080 / 1280x720 / 640x480 / 424x240 / 320x240 (MJPEG format),
      - Lens interface: C/CS,
      - Exposure: Automatic/Manual,
      - Exposure compensation: Supported,
      - White balance: Automatic / Manual, R, G, B adjustment supported,
      - Memory: Supports up to 64 GB,
    - DELL 4K Monitor:
      - Screen diagonal: 23.8",
      - Matrix: LED - IPS,
      - Screen resolution: 3840 x 2160 (UHD 4K),
      - Aspect ratio: 16:9,
      - Image frequency: 60 Hz,
      - Connectors: HDMI/MHL / DisplayPort / Mini DisplayPort / USB 3.2 (4 pcs.), USB-B 3.2 (1 pcs.),
- Device on a mobile 5-wheel base (2 braking wheels),
- Included:
  - Power cord,
  - New 32 GB memory card + adapter (microSD / microSDHC / microSDXC),
  - New remote control for remote control of camera functions,
  - New USB cable - 5 m,
- Dimensions: 60 kg,
- Weight: 70 x 80 x 150cm,
- Has an up-to-date inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

