



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67
E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006
kw@praiston.pl



OLYMPUS CLV-290 SL Light source (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 600 VA,
- Bulb: Xenon 300 Watt,
- Newly designed waterproof touch connector allows quick connection to light source and no oscilloscope cable required,
- Significant reduction in operating noise due to redesigned fan,
- Connecting peripherals avoids complicated cable connections and speeds up transmission speed,
- Improved AFI (**Auto Fluorescence Imaging**) results in less color splitting due to faster image tracking. With high image quality and minimized noise, it enables accurate observation of mucosal conditions,
- **Technical specifications:**
 - **Illumination:**
 - Lighting switching method: switch,
 - Brightness control: light path aperture control,
 - Cooling: forced air cooling,
 - NBI observation,
 - AFI observation,
 - IRI observation,
 - Emergency lamp: halogen lamp (in mirror) 12 V 35 W,
 - **Automatic brightness control:**
 - Servo throttle method,
 - Auto exposure 17 steps,
 - **Air supply:**
 - Diaphragm type pump,
 - Pressure switching;
 - Off,
 - Low,
 - Medium,
 - High,
 - **Memory settings:** settings (except filter settings) are saved even when the light source is turned off,
- **Included:**
 - Power cord,
- Dimensions: 37 x 47.6 x 15 cm,
- Weight: 18 KG,
- **It has a current inspection and is ready for operation,**
- **Issued Technical Passport (Service Report) valid for a period of 12 months,**
- **Warranty:**
 - **6-months for domestic market (Poland),**
 - **3-months for the international market,**
 - **Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,**
 - **The warranty period does not include bulbs and other light sources installed in the device,**
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

