



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



CARL ZEISS VISUREF 100 autorefractometer with keratometer (Reconditioned)

Reconditioned (used),

Technical condition: very good,

Visual condition: very good,

Real photos of the product,

Japanese production,

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 90 VA,

CARL ZEISS VISUREF 100

Provides precise and reliable pupil and iris examination,

Features:

Accurate and reliable examination in high quality,

Convenience of measurement and operation,

Clear information and clear visibility of data analysis,

Patient comfort due to ergonomic design,

Built-in 4 modes:

Refraction and combined keratometry (RK),

Refraction (REF),

Keratometry (KER),

Contact lens base curvature (CLBC),

Technical specifications:

Refraction measurement range:

Sphere: from -25.00 D to +25.00 D.,

Cylinder: 0.00 D to ± 10.00 D.,

Cylinder axis: 0° to 180°. (Gradual adjustment),

Vertex distance (VD): 0.0 / 10.0 / 12.0 / 13.5 / 15.0 mm,

Distance from the pupil: 10 - 85 mm,

Minimum pupil diameter: 2 mm,

Range of keratometry measurement:

Corneal curvature: 5.00 to 10.2 mm (gradual adjustment),

Corneal Refraction: From 33 D. to 67.5 D. (0.12 / 0.25 D. adjustment),

Corneal astigmatism: From 0 D. to - 15 D. (0.12 / 0.25 D. adjustment),

Cylinder axis: 0° to 180°. (gradual adjustment),

Corneal diameter: 2.0 to 12.0 mm. (gradual adjustment),

Chin adjustment in range: 6.5 cm,

Built-in thermal printer,

Built-in connectors:

RS232,

USB,

VIDEO,

Menu in language: English,

Included:

User manual in English (PDF),

Power cord,

Dimensions: 27.5 x 52.5 x 45 cm,

Weight: 18 KG,

Has a current inspection and is ready for operation,

Issued Technical Passport (Service Report) valid for a period of 12 months,

Warranty:

6-months for domestic market (Poland),

3-months for the international market,

Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,

Financing options (Poland only): Installments, Leasing, Loan,

