



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **UNIT Optical Classic Mini (New)**

New,

Polish production,

Characteristics:

It is characterized by an extremely simple and reliable construction.

It consists of a base, tabletop for 2 devices, projector mount or shelf for the projector and electrically lifted seat.

The chair is equipped with a high quality actuator made by Swiss company Schumo as a standard,

The seat is upholstered with skai leather in any colour from the RAL and ICA palettes,

Non-sliding top is fixed with a handle located on the side of the base body,

The unit can be easily and comfortably operated by means of a panel located on the table top,

Optionally the unit can be equipped with a halogen lamp and a phorofter arm,

Standard equipment:

Base,

Table top for 2 devices,

Mounting for projector or projector shelf,

Electrically raised seat,

Footrest,

Additional equipment (at extra charge):

Armrests,

Technical data:

Supply voltage 230 V, 50 Hz,

Power consumption 460 W,

Voltage available on the table top 230 V, 50 Hz + option 6-12 V,

Maximum load 80 kg,

Weight 180 kg,

Height 184 cm,

Dimensions 1240 x 1594 cm ,

It has a current Technical Passport,

12 months warranty,

Finance options (Poland only): instalments, leasing, loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN NEDERLANDS

МЫ ГОВОРИМ ПО РУССКИ

МИ РОЗМОВЛЯЄМО УКРАЇНСЬКОЮ

WE SHIP WORLDWIDE

