



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



LID Tina Halogen light (New)

- New,
- Made in France,
- Compact, sturdy and particularly easy to use halogen diagnostic light thanks to a ball joint that allows the head to rotate and tilt,
- Heat-generating halogen bulb,
- Technical data:
 - Light intensity: 300 Lumens,
 - Light color: 3000°K* (neutral white),
 - Color rendering index: IRC 100/100,
 - Bulb life: minimum 5,000 hours,
 - Electrical protection: insulation class II,
 - Lamp power - 20 W (GU 5.3 bicolor OSRAM Decostar ES SP 10° high efficiency source (with UV filter),
 - Standards: IEC 60 601 -1/ -2-41 IEC 60 598-2-25,
 - Power cord length: 3 meters,
 - Available colors : white, black,
- The standard length of the lamp is 650 mm, for an extra charge you can purchase a lamp with a length of 1000 mm,
- Dimensions :
 - Lamp head dimension: 70 x 70 mm,
 - Dimension of the base: 69 x 69 x 115 mm,
 - Weight : 1.3 / 1.7 kg,
 - Length : 650 / 1000 mm,
 - Inter-axial spacing (4 holes in the lamp base): 54.5 mm,
- Light field diameter :
 - 30 cm distance: 50,000 lux field illumination 5 cm
 - Distance 50 cm: 23,000 lux field illumination 10 cm,
 - Distance 100 cm: 6,000 lux field illumination 20 cm,
- Additional mounting accessories are required for the lamp , of your choice (at an extra charge):
 - Telescopic stand base 60-100 cm white metal, standard,
 - Telescopic stand base 60-100 cm metal white, standard -version with brakes in 2 wheels,
 - Telescopic stand base 90-130 cm metal white, standard,
 - Stand telescopic base 90-130 cm metal white, standard - version with brakes in 2 wheels,
 - Regular clamp - black,
 - Clamp for medical rails with vertical lamp outlet,
 - Universal clamp,
 - Wall bracket,
 - ARM wall bracket white (2x40cm),
 - ARM wall mount white (1x40cm),
 - Tabletop mount ARM white (1x60cm),
 - Metal base white / gray,
 - Plate with metal pipe in the middle ø16,
 - Plate with metal tube on the edge ø16,
 - Plate on ARM holder,
 - Female socket with adaptor plate Ø 16 mm x 27,
- It has a current Technical Passport issued,
- Warranty; 3 years,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

