



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Vera Magnifying LED light (New)

- New,
- A key tool for any analysis requiring the utmost precision and detail,
- LED-powered circular magnifying lamp with a 12 cm diameter, 2.25 X (5 diopters) non-distorting mineral glass lens and retractable protective cover,
- Provides white, uniform, non-glare light,
- Articulated arm and swivel joint allow quick and precise positioning of the lamp with one hand,
- Specifications:
 - Light intensity: 230 Lumens,
 - Light color: 6400 K,
 - Color rendering index: IRC 95/100,
 - Electricity consumption: 4 W,
 - LED life span: minimum 20,000 hours,
 - Illumination power at a distance of 10 cm: 2500 lux,
 - Electrical protection: insulation class I,
 - Power cord length: 1.5 meters,
 - Available colors : white,
 - Magnification power: 5 diopters,
 - Clamp included,
- Dimensions:
 - Articulated arm length: 860 mm,
 - Magnifier diameter 120 mm, Magnification: x 2.25,
 - Articulated arm 86 cm
- Additional accessories (at extra charge):
 - Heavy duty cart base for LED magnifying lamp,
- It has a current Technical Passport issued,
- Warranty: 3 years,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

