



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **LID Hydra Bi - Head LED light (New)**

- New,
- Made in France,
- A unique new special "beauty care" lamp model allows the user to position two lights on either side of the hand, avoiding the shadow formation that occurs when using only one light source,
- The Hydra light produces a scialitycal effect locally, allowing fine work to be done without shadows,
- The lamp heads are mounted on two individually adjustable flexible arms. The larger flexible arm connects the head unit to the base, providing support and maneuverability and ease of use,
- Specifications:
  - Light intensity: 420 Lumens,
  - Light color: 4500°K\* (neutral white),
  - Color Rendering Index: IRC 95/100,
  - Electricity consumption: 6,5 W,
  - LED lifetime: minimum 50,000 hours,
  - Electrical protection: insulation class II,
  - Standards: IEC 60 601 -1/ -2-41 IEC 60 598-2-25,
  - Power cord length: 3 meters,
  - Available colors : white, black,
- Dimensions:
  - Lamp head dimension: 60 x 100 mm,
  - Dimension of the base: 69 x 69 x 115 mm,
  - Length : flexible arm 100 cm + 2 x 25 cm,
- Diameter of the light field :
  - 30 cm distance: 20,000 lux field illumination 15 cm
  - Distance 50 cm: 7,000 lux field illumination 25 cm,
  - Distance 100 cm: 1,700 lux field illumination 35 cm,
- Additional mounting accessories are required for the lamp , of your choice (at an extra charge):
  - Telescopic stand base 60-100 cm white metal, heavy,
  - Telescopic stand base 60-100 cm white metal, heavy -version with brakes in 2 wheels,
  - Stand
  - Telescopic stand base 90-130 cm white metal, heavy,
  - Telescopic stand base 90-130 cm metal white, heavy - version with brakes in 2 casters,
  - Clamp for medical rails with vertical lamp outlet,
  - Universal clamp,
  - Wall bracket,
  - ARM wall bracket white (2x40cm),
  - Tabletop holder ARM white (1x60cm),
  - Plate with metal tube in the middle ø16,
  - Plate with metal tube on the edge ø16,
  - Plate on ARM holder,
  - Female socket with adaptor plate Ø 16mm x 27mm,
  - Adapter plate male rod Ø 15 mm x 30 mm,
- It has a valid Technical Passport issued,
- Warranty: 3 years,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

