



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **NGP 41 m ZU negatoscope (New)**

- A brand new product,
- Made in Poland,
- NGP 41 m ZU negatoscopes, are designed entirely for viewing mammographic X-ray images, It is a modern product ideally suited in improving cancer diagnosis,
- They also have the ability to narrow the area of the viewed image. This is undoubtedly a great asset in this type of device,

### **Advantages of using the NGP 41 m ZU negatoscope:**

- Light intensity 6800 cd/m<sup>2</sup> ± 10%,
- Day Light - 6500K daylight,
- Built-in four blinds,
- Excellent uniformity of screen illumination,
- High Frequency negatoscope,
- Powder coated case is very durable and dirt can be easily removed from it,
- The device has all required certificates,
- The operation of the negatoscope does not cause stroboscopic flicker effect,
- Very good parameters of this device allow detailed description of small features - such as micro calcifications,
- Fast ignition of fluorescent lamps,
- The ability to accurately "blend" the screen (also on its edges) is especially important for small areas,
- Placing images around the perimeter of the screen is possible, thanks to the x-ray film holder,
- Reducing power consumption by up to 25%,
- The movable version of the picture holder also allows viewing traditional 36 x 43 cm negatives,
- Smooth regulation of light intensity in the range of 10-100% of the maximum value allows to optimally adjust the brightness of the screen to the described images and general lighting,

### **Technical data:**

- Supply voltage: 230 V 50 Hz,
  - Power consumption: 380 VA,
  - Screen luminance: 6800 cd/m<sup>2</sup> ±10%,
  - Luminance regulation: Yes,
  - Regulation range: 10-100%,
  - Screen dimensions: 2 fields 108 x 60 cm,
  - Number of frames: 1,
  - Protection class: I,
  - Dimensions: 1400 x 940 x 120 mm,
  - Weight: 65 kg,
- Provided with an up-to-date Technical Passport,
  - Guarantee: 12 months,

