



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **Curing Light B-MAX (New)**

New

Italian production,

B-Max is a modern, technologically advanced curing light, light, easy to use, wireless,

B-Max uses new LED technology that ensures concentrated, low infrared emission, high light emission (spectrum 450/480 nm),

B-Max provides 1600 mW light emission,

B-Max includes a wireless handle with a wide color display, a long-lasting lithium battery that can be easily removed, a control panel for setting time, program setting, cycle start,

B-Max has 6 programs thanks to which you can choose from different power. B-Max has a shaped stand with built-in charger and LED indicator,

List of components:

Handle,

Battery charging stand,

Power Supply,

Battery,

fiber

Protective screen,

Technical data:

Dimensions of the handle (LxWxH): 182 x 95 x 22 (mm),

Stand dimensions (LxWxH): 170 x 180 x 145 (mm),

Handle weight: 170 grams,

Position weight: 240 grams,

Operating voltage: 6 V DC,

Battery: 3.7 V Lithium,

Light source: High power LED,

Frequency of waves: 420 ÷ 490 (nm),

Maximum power: 1600 mW / cm<sup>2</sup> (+/- 10%),

Has a current Technical Passport issued,

12 months warranty

