



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Automatic grinding machine i-Tronics 5100. Semi-automatic T82 scanocentroscope (New)

New,
French production,
The functions of the machine:
Processing every available material,
Machining of facets and 'flat',
Polishing,
Grooving,
Edge folding,
Manual mode for the position of the facet and groove, along with a change in its depth and width,
TEAM VIEW OPTION,
Scanocentroscope functions:
Mechanical scanning of full frames and demolens,
Optical demolens scanning (photographing lenses),
Semi-automatic lens blocking,
Monofocal, bifocal and progressive lens modes,
Advanced shape editing function,
TEAM VIEW OPTION,
Technical parameters of the machine:
Screen: 8.4 ", touchscreen,
Diameters: width 575 mm, depth 440 mm, height 620 mm,
Weight: 57 kg
Power consumption: 1350 W,
Voltage: 230-115 V ~ 50/60 Hz,
Technical parameters of the scanocentroscope:
Screen: 8.4 ", touchscreen
Diameters: 325 mm wide, 550 mm deep, 615 mm high,
Weight: 20 kg
Power consumption: 250 W,
Voltage: 230-115 V ~ 50/60 Hz,
Assembly, training included in the price,
Has a valid Technical Passport issued,
French manufacturer's warranty - 1 year,
Financing options: Installments, Leases, Loans

