



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Automatic grinding machine i-Tronics 5200. Automatic Tocentroscope T84 (New)

New,
French production,
The functions of the machine:
Processing of every available material,
Facet and flat machining,
Polishing,
Grooving,
Edge folding,
Drilling,
Manual mode for the position of the facet and groove, along with the change of its depth and width,
TEAM VIEW OPTION,
Scanocentroscope functions:
Mechanical scanning of full frames and demolens,
Optical scanning of demolens (photographing lenses),
Fully automatic lens blocking without having to select the optical center,
Automatic mode of monofocal, bifocal and progressive lenses,
Advanced shape editing function,
TEAM VIEW OPTION,
Technical parameters of the machine:
Screen: 8.4", touchscreen
Dimensions: width 575 mm, depth 440 mm, height 620 mm,
Weight: 57 kg
Power consumption: 1350 W,
Voltage: 230-115 V ~ 50/60 Hz,
Technical parameters of the scanocentroscope:
Screen: 8.4", touchscreen
Dimensions: 325 mm wide, 550 mm deep, 615 mm high,
Weight: 22 kg
Power consumption: 250 W,
Voltage: 230-115 V ~ 50/60 Hz,
Assembly, training included in the price,
Has a valid Technical Passport issued,
French manufacturer's warranty - 1 year,
Financing options: Installments, Leases, Loans

