



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **DRAGER EVITA XL respirator - ventilator (Reconditioned)**

Used, very good condition,  
German production,  
Number of hours worked: 66972 h,  
Power supply: 230 V and via the built-in battery + external battery in the trolley,  
Frequency: 50/60 Hz,  
Power consumption: 125 W,  
The Evita XL combines high performance with a range of advanced features to provide excellent respiratory therapy and easy handling for the entire ventilation process,  
By selecting how to present numerical, graphical, static or dynamic trend data, all measurement values and patient data are clearly displayed,  
The standard range of available functions has been supplemented by new, additional functions such as adjustment of end of inspiration criteria, optimized inspiratory/expiratory (I:E) ratio settings, easier lung aeration and an integral oxygen therapy function,  
Ventilation modes:  
IPPV, IPPVAssist/CMV, CMVAssist,  
SIMV, SIMVPsupp,  
MMV, MMVPsupp,  
BIPAP1), BIPAP1)ASB, BIPAP1)Assist / PCV+, PCV+Psupp, PCV+Assist,  
APRV,  
CPAP, CPAPASB / CPAP/Psupp, CPAP/Psupp,  
ILV,  
With the Lung Protection Package (LPP), the user has the option of using the pressure-volume loop (P/V) manoeuvre with low inspiratory flow to determine the optimum PEEP value and ventilation peak pressure,  
Additional functions: Autoflow, ATC,  
Weight range:  
Adults: 10 - 200 kg,  
Children: 3 - 15 kg,  
Equipped with a 15" TFT colour touch screen display,  
Clear menu in Polish,  
Upper top with usable dimensions: 36 x 24 cm,  
Sideways extendable tray with usable dimensions: 31 x 23 x 2 cm,  
Ergonomic handle for easy handling,  
Included:  
Patient's respiratory system with a 2 l breathing bag,  
Oxygen (O2) and air (AIR) supply hoses with optional endings on request (DIN or AGA),  
Sensor for measuring CO2,  
User manual in English (PDF),  
Rails for fixing additional accessories,  
Mobile trolley on four double casters with brakes,  
Dimensions:  
Without trolley: 530 x 315 x 450 mm,  
With a wheelchair: 540 x 530 x 1410 mm,  
Weight: 82.5 kg,  
Cat 05,  
He has a current Technical Passport issued,  
Warranty:  
6 months for the domestic market - Poland,  
1 month for the international market,  
Possibility of financing (Poland only): Instalments, Leasing, Loan

