



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Bactericidal double-functional UV-C STERILON FLOW 72W (New)

New,

Polish production,

Sterilon FLOW 72W UV-C lamps, using ultraviolet light (UVC), are one of the most effective devices able to remove viruses, bacteria, fungi or destroy the DNA or RNA of any microorganisms that will be exposed,

They are available in two versions: as single-function, flow-through - for air disinfection and as double-functional - which, when opened, can also be used for direct surface disinfection,

Lamps using the flow-through disinfection method are irreplaceable in rooms where it is necessary to clean the air safely and effectively in the presence of people,

Shielded UVC light does not get out of the lamp.

Due to forced circulation, the air passes through the inside of the lamp, where it is exposed and cleaned and then displaced outside. Just place the lamp in a convenient place.

The dual function of the UV-C STERILON FLOW lamp allows you to open it and use it also for direct surface disinfection. Simply point the UV lamp directly at the surface for a certain period of time in order to effectively kill germs. It should be remembered, however, that UVC light is not without a harmful effect on the skin or human eyes and that when using the lamp in this form it is necessary to observe safety rules concerning direct disinfection, i.e. not to be within the range of the light stream,

Recommended for use in service facilities (hairdressing salons, beauty parlors, manicure), health care facilities, public administration and education units, as well as for private use at home,

Features and advantages of UV-C STERILON FLOW 72W:

Flow air disinfection function,

One-way direct surface disinfection function,

Type of light: ultraviolet UV-C,

Dust filter,

Space for HEPA filter,

Case color: white,

Front color: zinc plated silver,

Airflow: 110 m³/h,

Service life: 9000h,

Supply voltage: 220-240V,

Degree of tightness: IP20,

Power supply cable 2m,

Weight 6.6 kg,

ON-OFF switch,

Additional accessories: castors, HEPA filter, sensor switching the lamp on after detection of presence (flow disinfection), timer switching the lamp on for a specified period of time with an additional safety sensor, timer for operation time

Dimensions (A/B/C) [mm]: 160x160x724,

Warranty 12 months

